



### LED torch C series, Type: C7R



#### Order data

Order number	081447 C7R
GTIN	4058205038317
Item class	04B

#### Description

##### Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

##### Supplied with:

Including 1 pc. Li-ion rechargeable battery type 18650 3.7 V, 1 pc. Floating Charge System, 1 pc. hand loop, 1 pc. voucher for belt bag.

##### Note:

**2+5-year warranty upon registration on [www.ledlenser.com](http://www.ledlenser.com).**

Unless otherwise specified below, we provide a manufacturer's warranty on our products of

- **seven years if the product is registered online within 12 weeks from the date of purchase**
- **two years if the product is not registered online or is not registered online in a timely manner; we also grant a warranty period of two years (without extension of the warranty period, no registration), calculated from the date of purchase for proper functioning of rechargeable batteries, the Powercase and the battery box.**

#### Technical description

Overall length	166 mm
Weight	210 g
Illumination range	40 - 210 m
Illumination time stage 2	5 h
Rapid Focus	yes

## Data sheet

Replaceable battery	yes
Battery voltage	3.7 V
Advanced Focus System (AFS)	yes
Smart Light Technology (SLT)	yes
Illumination time	2 - 40 h
Illumination	20 - 1000 lm
Including belt pocket	yes
Number of rechargeable batteries contained	1
CRI value	65
Bulb	LED module
Illumination step 2	1000 lm
Type of rechargeable battery	Lithium-ion
Power supply	Battery-powered
IP Index of Protection	IP 54
International size	18650
Battery capacity	2.5 Ah
Series	C series
Colour of housing	BLACK
Light colour	cold white
Manufacturer's designation	C7R
Illumination step 3	250 lm
Head Ø	37 mm
Illumination time stage 3	2 h
Type of product	Torch

### Suitable products

No Shop URL available for: 081447 C7R