



LED torch C series, Type: C7



Order data

Order number	081447 C7
GTIN	4058205038379
Item class	04B

Description

Function:

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Includes 4 pcs. AAA LR03 1.5 V battery, 1 pc. hand loop, 1 pc. voucher for belt bag.

Note:

2+5-year warranty upon registration on www.ledlenser.com.

Unless otherwise specified below, we provide a manufacturer's warranty on our products of

- **seven years if the product is registered online within 12 weeks from the date of purchase**
- **two years if the product is not registered online or is not registered online in a timely manner; we also grant a warranty period of two years (without extension of the warranty period, no registration), calculated from the date of purchase for proper functioning of rechargeable batteries, the Powercase and the battery box.**

Technical description

International size	LR3
CRI value	70
Illumination	40 lm
Illumination step 3	400 lm
Overall length	140 mm
Head Ø	37 mm

Data sheet

#Number of batteries contained	4
Including belt pocket	yes
Illumination time	1 - 25 h
Illumination range	100 - 300 m
Manufacturer's designation	C7
Power supply	Battery-powered
Battery type	Micro, AAA
Bulb	LED module
Rapid Focus	yes
Illumination time stage 3	1 h
Light colour	cold white
Weight	175 g
Illumination time stage 2	2 h
Advanced Focus System (AFS)	yes
Series	C series
Illumination step 2	250 lm
Colour of housing	BLACK
IP Index of Protection	IP 54
Type of product	Torch

Suitable products

No Shop URL available for: 081447 C7