

**LED torch C series, Type: C3R****Order data**

Order number	081447 C3R
GTIN	4058205038409
Item class	04B

Description**Function:**

IP54: Protected against splashed water from all directions and protected against penetration of dust into the inside (protected against dust), also completely protected against touching.

Supplied with:

Includes 1 pc. Li-ion rechargeable battery type 10440 3.7 V, 1 pc. charging station, 1 pc. hand loop.

Note:

2+5-year warranty upon registration on www.ledlenser.com.

Unless otherwise specified below, we provide a manufacturer's warranty on our products of

- **seven years if the product is registered online within 12 weeks from the date of purchase**
- **two years if the product is not registered online or is not registered online in a timely manner; we also grant a warranty period of two years (without extension of the warranty period, no registration), calculated from the date of purchase for proper functioning of rechargeable batteries, the Powercase and the battery box.**

Technical description

Number of rechargeable batteries contained	1
Illumination step 2	140 lm
Power supply	Battery-powered
Head Ø	20 mm
Battery capacity	0.32 Ah

Data sheet

Colour of housing	BLACK
Rapid Focus	yes
International size	10440
Battery voltage	3.7 V
Overall length	102 mm
Light colour	cold white
Manufacturer's designation	C3R
Illumination time stage 2	2 h
IP Index of Protection	IP 54
Illumination time	2 - 6 h
Bulb	LED module
Series	C series
Replaceable battery	yes
Including belt pocket	no
Type of rechargeable battery	Lithium-ion
Illumination range	40 - 100 m
Weight	42 g
Advanced Focus System (AFS)	yes
CRI value	65
Illumination	20 - 140 lm
Type of product	Torch

Suitable products

No Shop URL available for: 081447 C3R