


KOMET® recessing bar Form f, Type: B00

Order data

Order number	240078 B00
GTIN	4047109004009
Item class	24H

Description
Version:

Microscopically tested, precise cutting profile. Cost-efficient due to multiple regrinding of the cutting face.

Sizes with suffix **L** = **extended shank**.

Tool material:

HSS/Co10 – for difficult to machine materials.

Note:

For suitable boring bar holders see No. 240070 and No. 240072.

Tool material: HSS Co 10

Boring depth: 10 mm

for bores from \varnothing : 2.5 mm

Overall length: 50 mm

Shank \varnothing : 8 mm

Technical description

for bores from \varnothing	2.5 mm
Boring depth	10 mm
Type	B00
Overall length	50 mm
Shank \varnothing	8 mm
Tool material	HSS Co 10
Type of product	Cutter insert for turning

