



## KOMET® recessing bar Form f, Type: B05L



### Order data

Order number	240078 B05L
GTIN	4047109017573
Item class	24H

### Description

#### Version:

Microscopically tested, precise cutting profile. Cost-efficient due to multiple regrinding of the cutting face.

Sizes with suffix **L** = **extended shank**.

#### Tool material:

**HSS/Co10** – for difficult to machine materials.

#### Note:

**For suitable boring bar holders see No. 240070 and No. 240072.**

Tool material: HSS Co 10

Boring depth: 80 mm

for bores from  $\varnothing$ : 12 mm

Overall length: 125 mm

Shank  $\varnothing$ : 8 mm

### Technical description

for bores from $\varnothing$	12 mm
Boring depth	80 mm
Overall length	125 mm
Type	B05L
Shank $\varnothing$	8 mm
Tool material	HSS Co 10
Type of product	Cutter insert for turning

