



## KOMET® recessing bar Form f, Type: B06



### Order data

Order number	240078 B06
GTIN	4047109016354
Item class	24H

### Description

#### Version:

Microscopically tested, precise cutting profile. Cost-efficient due to multiple regrinding of the cutting face.

Sizes with suffix **L** = **extended shank**.

#### Tool material:

**HSS/Co10** – for difficult to machine materials.

#### Note:

**For suitable boring bar holders see No. 240070 and No. 240072.**

Tool material: HSS Co 10

Boring depth: 60 mm

for bores from Ø: 14 mm

Overall length: 95 mm

Shank Ø: 10 mm

### Technical description

Type	B06
Overall length	95 mm
Boring depth	60 mm
for bores from Ø	14 mm
Shank Ø	10 mm
Tool material	HSS Co 10
Type of product	Cutter insert for turning

