

**Tee bolt (8.8.) complete, Type: 2020115****Order data**

Order number	375301 2020115
GTIN	4069515011969
Item class	32H

Description**Version:**

T-slot bolt, quenched and tempered, black, strength class 8.8.

Standard:

DIN 787

Supplied with:

Complete, with washer No. 375341

Optional extras:

Washers, see No. 35341 and tall nuts, see No. 375386.

Note:

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

Technical description

Height k	12 mm
Type	787
Thread length b	70 mm
T-slot nominal size	20 mm
narrow nut width a	19.7 mm
Nut width e	32 mm
Thread G	M20

Data sheet

Length L	80 mm
Type of product	T-bolt