

**Tee bolt (8.8.) complete, Type: 2824210****Order data**

|              |                |
|--------------|----------------|
| Order number | 375301 2824210 |
| GTIN         | 4069515012072  |
| Item class   | 32H            |

**Description****Version:**

T-slot bolt, quenched and tempered, black, strength class 8.8.

**Standard:**

**DIN 787**

**Supplied with:**

Complete, with washer No. 375341

**Optional extras:**

Washers, see No. 35341 and tall nuts, see No. 375386.

**Note:**

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

**Technical description**

|                     |         |
|---------------------|---------|
| Thread length b     | 130 mm  |
| Nut width e         | 44 mm   |
| Type                | 787     |
| Length L            | 210 mm  |
| T-slot nominal size | 28 mm   |
| narrow nut width a  | 27.7 mm |
| Thread G            | M24     |

## Data sheet

|                 |        |
|-----------------|--------|
| Height k        | 18 mm  |
| Type of product | T-bolt |