


**KOMET® recessing bar Form f, Type: B06L**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 240078 B06L   |
| GTIN         | 4047109017610 |
| Item class   | 24H           |

**Description**
**Version:**

Microscopically tested, precise cutting profile. Cost-efficient due to multiple regrinding of the cutting face.

Sizes with suffix **L** = **extended shank**.

**Tool material:**

**HSS/Co10** – for difficult to machine materials.

**Note:**

**For suitable boring bar holders see No. 240070 and No. 240072.**

Tool material: HSS Co 10

Boring depth: 90 mm

for bores from Ø: 14 mm

Overall length: 125 mm

Shank Ø: 10 mm

**Technical description**

|                  |                           |
|------------------|---------------------------|
| Overall length   | 125 mm                    |
| Type             | B06L                      |
| for bores from Ø | 14 mm                     |
| Boring depth     | 90 mm                     |
| Shank Ø          | 10 mm                     |
| Tool material    | HSS Co 10                 |
| Type of product  | Cutter insert for turning |

