



KOMET® roughing bar Form g, Type: B04L



Order data

Order number	240074 B04L
GTIN	4047109017757
Item class	24H

Description

Version:

Microscopically tested, precise cutting profile. Cost-efficient due to multiple regrinding of the cutting face.

Sizes with suffix **L** = **extended shank**.

Tool material:

HSS/Co10 – for difficult to machine materials.

Note:

For suitable boring bar holders see No. 240070 and No. 240072.

Tool material: HSS Co 10

Boring depth: 80 mm

for bores from Ø: 9 mm

Overall length: 125 mm

Shank Ø: 8 mm

Technical description

for bores from Ø	9 mm
Type	B04L
Overall length	125 mm
Boring depth	80 mm
Shank Ø	8 mm
Tool material	HSS Co 10
Type of product	Cutter insert for turning

