


**KOMET® recessing bar Form f, Type: B02L**

**Order data**

Order number	240078 B02L
GTIN	4047109017450
Item class	24H

**Description**
**Version:**

Microscopically tested, precise cutting profile. Cost-efficient due to multiple regrinding of the cutting face.

Sizes with suffix **L** = **extended shank**.

**Tool material:**

**HSS/Co10** – for difficult to machine materials.

**Note:**

**For suitable boring bar holders see No. 240070 and No. 240072.**

Tool material: HSS Co 10

Boring depth: 24 mm

for bores from  $\varnothing$ : 5 mm

Overall length: 125 mm

Shank  $\varnothing$ : 8 mm

**Technical description**

for bores from $\varnothing$	5 mm
Overall length	125 mm
Boring depth	24 mm
Type	B02L
Shank $\varnothing$	8 mm
Tool material	HSS Co 10
Type of product	Cutter insert for turning

