

**Digital lever dial indicator, contact point length 41.24 mm, Measuring range (reversible) / housing Ø: 2,2/45mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 436506 2,2/45 |
| GTIN         | 4059192074081 |
| Item class   | 43A           |

**Description****Version:**

Digital lever dial indicator with digital and analogue display **1/1000 reading**.

**Measurement mode.** Normal / MIN / MAX / MAX-MIN. A correction factor can be entered.

**Supplied with:**

1 battery No. 081560 size CR2032, clamping spigot Ø 8 mm, contact point key, carbide contact point Ø 2 mm.

**Optional extras:**

Data cable No. 498951. See No. 436210; 436240 for spare contact points.

**Technical description**

|                       |               |
|-----------------------|---------------|
| Scale divisions       | 0.001 mm      |
| Variation range $f_e$ | 10 $\mu$ m    |
| Gauging force         | 0.06 N        |
| Pivot range           | 2×110 degrees |

## Data sheet

|                        |                      |
|------------------------|----------------------|
| Clamping shank Ø h6    | 8 mm                 |
| Hysteresis error $f_u$ | 5 $\mu$ m            |
| Standard               | Works standard       |
| Reversible reading     | mm / inch            |
| Interface              | Digimatic interface  |
| Interface              | USB interface        |
| Measurement technology | digital              |
| Calibration            | C5                   |
| Type of product        | Lever dial indicator |