

**Digital lever dial indicator, contact point length 14.5 mm, Measuring range (reversible) / housing Ø: 0,9/45mm****Order data**

Order number	436501 0,9/45
GTIN	4059192074074
Item class	43A

Description**Version:**

Digital lever dial indicator with digital and analogue display **1/1000 reading**.

Measurement mode. Normal / MIN / MAX / MAX-MIN. A correction factor can be entered.

Supplied with:

1 battery No. 081560 size CR2032, clamping spigot Ø 8 mm, contact point key, carbide contact point Ø 2 mm.

Optional extras:

Data cable No. 498951. See No. 436210; 436240 for spare contact points.

Technical description

Scale divisions	0.001 mm
Hysteresis error f_u	3 μ m
Gauging force	0.15 N
Pivot range	2×110 degrees

Variation range f_e	5 μm
Clamping shank $\varnothing$ h6	8 mm
Standard	Works standard
Reversible reading	mm / inch
Interface	Digimatic interface
Interface	USB interface
Measurement technology	digital
Calibration	C5
Type of product	Lever dial indicator

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/436501-0,9/45>