



## LED torches, Manufacturer's designation: P3



### Order data

Order number	081485 P3
GTIN	4058205009393
Item class	04B

### Description

#### Version:

LED lenses are amongst the technology leaders for LED torches. Within the **splash-proof aluminium housing**, all the contacts are gold-plated, **high-quality lenses** gather the light uniformly and without losses. All these high-class torches incorporate the patented **Advanced Focus System**.

High-performance line of LED LENSES for general- purpose use. Drop tested from a 1 m height.

- **Advanced Focus System (AFS)**

**The Advanced Focus System is a combination of lens and reflector, thus incorporating the advantages of both systems. The result is an outstanding concentration of light in focus, together with a largely homogeneous unfocussed light beam. This makes the AFS one of the best focussing systems in the world for LED lamps.**

- **Rapid Focus**

**Conventional focussing systems with twist knobs must be operated manually with both hands. Rapid Focus, on the other hand, allows quick adjustment of the light beam with only one hand.**

#### Supplied with:

Including batteries.

#### Note:

In general, manufacturer provides a warranty on this product of **five years** (seven years with online registration).

Illumination: 25 lm

Working life: 6 h

Lighting life stage 2: 6 h

Advanced Focus System (AFS): yes

Rapid Focus: yes

Number of batteries contained: 1

## Technical description

Battery type	LR3
Manufacturer's designation	P3
Advanced Focus System (AFS)	yes
Number of batteries contained	1
Working life	6 h
Head Ø	19 mm
Including belt pocket	yes
Weight	35 g
Illumination	25 lm
Rapid Focus	yes
Lighting life stage 2	6 h
Overall length	96 mm

## Accessories

Alkaline-manganese batteries International size LR3	081556 LR3
---	------------