

**Tee bolt (8.8.) single, Type: 1412125****Order data**

Order number	375306 1412125
GTIN	4069515014557
Item class	32H

Description**Version:**

T-slot bolt, quenched and tempered, black, strength class 8.8.

Standard:

DIN 787

Supplied with:

Single, without nut and washer.

Optional extras:

Washers, see No. 35341 and tall nuts, see No. 375386.

Note:

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

Technical description

narrow nut width a	13.7 mm
Thread length b	80 mm
Type	787
T-slot nominal size	14 mm
Nut width e	22 mm
Thread G	M12
Height k	8 mm

Data sheet

Length L	125 mm
Type of product	T-bolt