

**Tee bolt (8.8.) single, Type: 2424125****Order data**

Order number	375306 2424125
GTIN	4069515014700
Item class	32H

Description**Version:**

T-slot bolt, quenched and tempered, black, strength class 8.8.

Standard:

DIN 787

Supplied with:

Single, without nut and washer.

Optional extras:

Washers, see No. 35341 and tall nuts, see No. 375386.

Note:

· **Reading example – size 6625 means: T-slot = 6 mm, thread G = M6, length L = 25 mm.**

Technical description

Type	787
Nut width e	40 mm
Thread length b	75 mm
Length L	125 mm
narrow nut width a	23.7 mm
T-slot nominal size	24 mm
Thread G	M24

Data sheet

Height k	16 mm
Type of product	T-bolt