



XL Step work platform, with double-sided access, Number of steps including platform: 2X4



Order data

Order number	966151 2X4
GTIN	4003866414116
Item class	96Z

Description

Version:

Robust, foldable work platform with double-sided access, large platform and abrasion-resistant anodised stiles. Extra-deep steps (92 mm) provide a comfortable and secure footing. Optimum stability due to rigid connections on both sides with pressure stiffening. Large end cap made of 2-component plastic, also suitable for working on grid/grille surfaces.

Standard:

DIN EN 14183.

Technical description

Platform height without railing	0.99 m
Ladders and platforms load capacity	150 kg
Working height approx.	2.99 m
Weight	9.3 kg
Handrail	no

Data sheet

height-adjustable	no
Type of step	step
with platform railings	no
Material	Anodised aluminium
Platform depth	300 mm
outer width at bottom	0.96 m
Accessibility	double-sided
Knee bar	no
Platform width	600 mm
Number of steps including platform	2×4
Rollers	no
Rung/step depth	92 mm
Type of product	Work platform