



XL Step work platform, with double-sided access, Number of steps including platform: 2X2



Order data

Order number	966151 2X2
GTIN	4003866414093
Item class	96Z

Description

Version:

Robust, foldable work platform with double-sided access, large platform and abrasion-resistant anodised stiles. Extra-deep steps (92 mm) provide a comfortable and secure footing. Optimum stability due to rigid connections on both sides with pressure stiffening. Large end cap made of 2-component plastic, also suitable for working on grid/grille surfaces.

Standard:

DIN EN 14183.

Technical description

Working height approx.	2.49 m
Platform height without railing	0.49 m
outer width at bottom	0.8 m
with platform railings	no
Handrail	no
Ladders and platforms load capacity	150 kg

Data sheet

Weight	5.6 kg
Knee bar	no
Rollers	no
Platform width	600 mm
Material	Anodised aluminium
height-adjustable	no
Rung/step depth	92 mm
Platform depth	300 mm
Type of step	step
Number of steps including platform	2×2
Accessibility	double-sided
Type of product	Work platform