



## Masterflex Plus S telescopic platform ladder, Number of steps including platform: 5



### Order data

|              |               |
|--------------|---------------|
| Order number | 966284 5      |
| GTIN         | 4003866411566 |
| Item class   | 96Z           |

### Description

#### Version:

Telescopic platform ladder with guard rails around and automatic saloon door. Easy adjustment of height with 1-hand handle. With swing-out stabilisers with 1-hand operation. 2 running wheels allow the ladder to be moved easily, even when fully extended. Wide tread due to 60 mm deep steps. Platform made of glued plywood panel. Roller Ø 200 mm. With plastic shelf.

#### Standard:

EN 131-7.

### Technical description

|                   |              |
|-------------------|--------------|
| wheeled           | yes          |
| Platform width    | 400 mm       |
| Weight            | 29.5 kg      |
| height-adjustable | yes          |
| Accessibility     | single-sided |

## Data sheet

|                                           |                      |
|-------------------------------------------|----------------------|
| Standard                                  | EN 131-7             |
| Platform depth                            | 550 mm               |
| Platform height without railings inserted | 0.78 / 1.03 / 1.28 m |
| Approx. max. working height               | 3.28 m               |
| Footprint – depth (stabilisers extended)  | 1.8 m                |
| Max. height including railing             | 2.31 m               |
| Footprint – width (stabilisers extended)  | 2.1 m                |
| Ladders and platforms load capacity       | 150 kg               |
| Two hands free principle                  | yes                  |
| Type of product                           | Platform ladder      |