



Screwdriver for slot-head, with 3-component SwissGrip Evo handle, Blade width b: 4mm



Order data

Order number	660042 4
GTIN	7610733296743
Item class	63E

Description

Version:

Blade of PB Swiss Tools special alloy combines maximum hardness with exceptional toughness. Surface nickel-plated and chrome-plated. Black tip. Stepped plane parallel tips provide full-surface instead of linear contact, enabling higher torque transmission.

SwissGrip Evo power grip allows transmission of the required torque with no problems, even with wet or oily hands. Work without getting tired thanks to modified circular shape. High-tech 3-component materials improve the chemical and mechanical resistance. Handle with "Rainbow" colour coding for finding the correct drive size quickly

Advantage:

- **Stepped plane parallel tips provide full-surface instead of linear contact, enabling higher torque transmission.**
- **No cam-out effect.**
- **Tips perfectly fit standard and non-standard screw slot sizes.**
- **Smooth, burr-free rounding of the end of the handle prevents friction in the palm of the hand.**
- **Rounded ergonomic shape with comfortable easy-grip surface ensures non-fatiguing working and high torque transmission.**
- **Non-roll flats.**
- **Marked with drive symbol and size.**

Technical description

overall length	195 mm
Blade designation	2
Blade tip	black

Data sheet

Tip thickness a	0.6 mm
Blade length	100 mm
Drive profile	Slot-head screwdriver
Type of shank	round
Impact cap	no
Material	PB Swiss Tools special alloy.
Material of handle	Elastomer
Surface	nickel-plated and chrome-plated
Type of product	Screwdrivers