

**Garant**
**Screw-on toolholder, right-hand, Shank / insert size: 20/09 mm**

**Order data**

Order number	260006 20/09
GTIN	4045197651631
Item class	21T

**Description**

Screw-on toolholder 20/09 mm ISO code toolholder: SCLCR/L 2020K09  
 suitable indexable insert: CC.. 09T3..  
 Functional width L<sub>4</sub>: 25 mm  
 Head length L<sub>1</sub>: 17 mm  
 Overall length L: 125 mm  
 Pack of insert screws: 269028 2

**Technical description**

Shank size	20 mm
Head length L <sub>1</sub>	17 mm
Shim screw	269013 2
Shim	269005 1
Functional width L <sub>4</sub>	25 mm
suitable indexable insert	CC.. 09T3..
ISO code toolholder	SCLCR/L 2020K09
Pack of insert screws	269028 2
Insert size	9 mm
Overall length L	125 mm
Application type	right-hand

Standard	DIN ISO 5610
Through-coolant	no
Setting angle $\kappa$	95 °
Type of product	Boring bar

## Accessories

Set of insert screws Type 2	269028 2
Shim	269000
Shim screw	269200
Shim Type 1	269005 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Shim screw Type 2	269013 2
Set of insert screws Type 22	269028 22
PrecisionBit for Torx®, shank E 6.3 Torx® profile TX15	674248 TX15
Set of insert screws 10 pieces	269400