


KUB Pentron® indexable drill ABS® shank, 5×D, Ø DC: 25,5mm

Order data

Order number	236604 25,5
GTIN	4047109181861
Item class	24P

Description
Version:
Bore tolerance: D – 0.1 / + 0.35

Application:

With indexable inserts No. 236605 – 236610.

Recommendation:
When spot-drilling reduce the feed rate to 70%.

Note:

- **For use only under stable machining conditions.**
- **Version 2×D and 3×D with ABS® shank available on request.**
- **Offset-axis drilling up to $V_{max} = 0.25$ mm.**
- **Maximum $\varnothing = D + 0.5$ mm achievable by offsetting.**
- **Version with PSC shank available on request.**

Technical description

ISO code indexable insert	SOGX 080308 24-...
Reach L ₁	130 mm
Number of cutting edges Z	1
ABS® shank Ø D _s	50 mm
Pack of insert screws	239652 8IP1 (1.3 Nm)
Series	KUB Pentron®
Nominal Ø D	25.5

for inch Ø	1 in
Overhang L _A	163 mm
Drill depth for indexable insert drill up to	5×D
Shank	ABS
Use for drilling	limited centre drilling
Use for drilling	limited convexity
Use for drilling	limited cross-drilling
Use for drilling	limited drilling through a stack
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Through-coolant	yes
Machining strategy	HPC
Type of product	Indexable drill

Accessories

Torx Plus® insert screw set 10 pieces Drive 8IP1	239652 8IP1
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Torque screwdriver, fixed setting set torque 1,3 N·m	211750 1,3