


**KUB Pentron® indexable drill ABS® shank, 5×D, Ø DC: 41,5mm**

**Order data**

Order number	236604 41,5
GTIN	4047109201897
Item class	24P

**Description**
**Version:**
**Bore tolerance:** D – 0.1 / + 0.35

**Application:**

With indexable inserts No. 236605 – 236610.

**Recommendation:**
**When spot-drilling** reduce the feed rate to 70%.

**Note:**

- **For use only under stable machining conditions.**
- **Version 2×D and 3×D with ABS® shank available on request.**
- **Offset-axis drilling up to  $V_{max} = 0.25$  mm.**
- **Maximum  $\varnothing = D + 0.5$  mm achievable by offsetting.**
- **Version with PSC shank available on request.**

**Technical description**

Number of cutting edges Z	1
Pack of insert screws	239652 20IP (6.3 Nm)
ISO code indexable insert	SOGX 120408 42-...
Reach L <sub>1</sub>	210 mm
ABS® shank Ø D <sub>s</sub>	63 mm
Series	KUB Pentron®
Nominal Ø D	41.5

Overhang L <sub>A</sub>	254 mm
Drill depth for indexable insert drill up to	5×D
Shank	ABS
Use for drilling	limited centre drilling
Use for drilling	limited convexity
Use for drilling	limited cross-drilling
Use for drilling	limited drilling through a stack
Use for drilling	limited drilling with oblique exit
Use for drilling	limited cross-drilling
Through-coolant	yes
Machining strategy	HPC
Type of product	Indexable drill

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 20IP	674252 20IP
Torx Plus® insert screw set 10 pieces Drive 20IP	239652 20IP
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600