

Power bank energy box, Type: 10



Order data

Order number	081604 10
GTIN	4008496018895
Item class	08C

Description

Version:

The VARTA Energy power bank with 4 ports (1x micro USB input, 2x USB A output, 1x bi-directional USB C port) offers the perfect capacity for every individual energy requirement with 10,000 mAh.

Description:

- **Powerful power bank with 4 ports (1x micro USB input, 2x USB A output, 1x bi-directional USB Type C port)**
- **Battery: Li polymer 3.7 V, 10000 mAh 37 Wh**
- **Pass-through charging function: Charge the powerbank and smartphone at the same time**
- **Fast charging due to the popular USB Type C 5 V/ 3.0 A output**
- **Ideal for on the go: Charges 3 devices at the same time**
- **The charge and discharge level is indicated by 4 white LEDs**
- **With the latest "VARTA Advanced Safety Technology"**

Supplied with:

Supplied with USB Type C charging cable

Technical description

Number of rechargeable batteries contained	1
Type of rechargeable battery	Lithium-ion
Battery capacity	10 Ah

Data sheet

Height	195 mm
Battery voltage	3.7 V
Width	31 mm
Number of charging slots for USB	4
Type of product	Charger