

**Combination hammer, Hammer head Ø: 27mm****Order data**

Order number	754890 27
GTIN	
Item class	73V

Description**Version:**

Combined **engineer's hammer and soft hammer**, sides additionally with ground striking faces for working in confined spaces. Head made of highly tempered steel with an exchangeable set of inserts made of wear-resistant nylon – shore hardness approx. 68D. With unbreakable "Ultratec" glass fibre handle.

Spare part:

Nylon insert No. 754895.

Technical description

Hammer head Ø	27 mm
Weight	0.49 kg
Head length with inserts	92 mm
Hammer head dimensions	27×27 mm
Overall length	290 mm
Series	Ultratec DUO
dead-blow	no
Type of product	Hammer