

 KOMET

**KOMET® internal thread boring bar, right-hand Form 60° (metric), Type: B06**

**Order data**

Order number	240084 B06
GTIN	4047109017054
Item class	24H

**Description**
**Version:**

Microscopically tested, precise cutting profile. Cost-efficient due to multiple regrinding of the cutting face.

Sizes with suffix **L** = **extended shank**.

**Tool material:**

**HSS/Co10** – for difficult to machine materials.

**Note:**

**For suitable boring bar holders see No. 240070 and No. 240072.**

**Technical description**

for bores from Ø	14 mm
Type	B06
Boring depth	60 mm
Overall length	95 mm
for pitches up to	3 mm
Shank Ø	10 mm
Tool material	HSS Co 10
Type of product	Cutter insert for turning