

**Garant**
**Boring bar HSS, right-hand, Shank  $\varnothing$  / insert size: 0610/03mm**

**Order data**

Order number	260022 0610/03
GTIN	4045197651976
Item class	21T

**Technical description**

Minimum pre-drill $\varnothing D_{\min}$	7 mm
Head length $L_1$	24 mm
Centre offset $L_3$	2.5 mm
Pack of insert screws	269028 13
Insert size	3 mm
suitable indexable insert	CC.. 0301..
Neck width $L_4$	6 mm
ISO code toolholder	AH0610H SCLCR/L03
Overall length $L$	100 mm
Clamping height $L_2$	9 mm
Setting angle $\kappa$	95 degrees
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Set of insert screws Type 13	269028 13
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500