

Garant
Screw-on toolholder, left-hand, Shank / insert size: 16/09mm

Order data

| | |
|--------------|---------------|
| Order number | 260007 16/09 |
| GTIN | 4045197651723 |
| Item class | 21T |

Technical description

| | |
|---------------------------------|-------------------------------|
| suitable indexable insert | CC.. 09T3.. |
| Functional width L ₄ | 20 mm |
| Pack of insert screws | 269028 2 |
| ISO code toolholder | SCLCR/L 1616H09 |
| Shim screw | 269013 2 |
| Insert size | 9 mm |
| Shim | 269005 1 |
| Shank size | 16 mm |
| Head length L ₁ | 17 mm |
| Overall length L | 100 mm |
| Series | QuickTurn |
| Standard | DIN ISO 5610 |
| Application type | left-hand |
| Through-coolant | no |
| Setting angle κ | 95 degrees |
| Application | External longitudinal turning |

| | |
|-----------------|-------------------------------|
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|-------------|
| Shim screw Type 2 | 269013 2 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15 | 674248 TX15 |
| Set of insert screws Type 2 | 269028 2 |
| Shim Type 1 | 269005 1 |
| Set of insert screws Type 22 | 269028 22 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |