

**Garant**
**Boring bar HSS, left-hand, Shank  $\varnothing$  / insert size: 16/09mm**

**Order data**

Order number	260023 16/09
GTIN	4045197652171
Item class	21T

**Technical description**

Pack of insert screws	269028 8
Centre offset $L_3$	11 mm
ISO code toolholder	AH16Q SCLCR/L09
Minimum pre-drill $\varnothing D_{\min}$	18 mm
suitable indexable insert	CC.. 09T3..
Overhang $L_1$	80 mm
Insert size	9 mm
Overall length $L$	180 mm
Clamping height $L_2$	15 mm
Setting angle $\kappa$	95 degrees
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

---

**Accessories**

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15

674248 TX15

Set of insert screws Type 8

269028 8

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500