

Garant
Boring bar carbide, right-hand, Shank \varnothing / insert size: 5/03mm

Order data

Order number	260016 5/03
GTIN	4045197651785
Item class	21T

Technical description

suitable indexable insert	CC.. 0301..
Minimum pre-drill $\varnothing D_{\min}$	6 mm
Insert size	3 mm
ISO code toolholder	E05H SCLCR/L03
Centre offset L_3	3 mm
Head length L_1	10 mm
Pack of insert screws	269028 19
Overall length L	100 mm
Clamping height L_2	4.8 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	5 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6

Set of insert screws Type 19

269028 19

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500