

Garant**Boring bar HSS, left-hand, Shank \varnothing / insert size: 0410/03mm****Order data**

Order number	260023 0410/03
GTIN	4045197652089
Item class	21T

Technical description

Pack of insert screws	269028 13
Centre offset L_3	2.5 mm
suitable indexable insert	CC.. 0301..
ISO code toolholder	AH0410H SCLCR/L03
Head length L_1	24 mm
Minimum pre-drill $\varnothing D_{\min}$	5 mm
Neck width L_4	4 mm
Insert size	3 mm
Overall length L	100 mm
Clamping height L_2	9 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Set of insert screws Type 13	269028 13
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500