

**Garant**
**Boring bar HSS, left-hand, Shank  $\varnothing$  / insert size: 20/09mm**

**Order data**

Order number	260023 20/09
GTIN	4045197652188
Item class	21T

**Technical description**

Minimum pre-drill $\varnothing D_{\min}$	23 mm
ISO code toolholder	AH20R SCLCR/L09
suitable indexable insert	CC.. 09T3..
Centre offset $L_3$	13 mm
Insert size	9 mm
Pack of insert screws	269028 8
Overhang $L_1$	100 mm
Overall length $L$	200 mm
Clamping height $L_2$	18 mm
Setting angle $\kappa$	95 degrees
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring bar
-----------------	------------

---

## Accessories

Set of insert screws Type 8	269028 8
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500