

Garant
Boring bar carbide, right-hand, Shank \varnothing / insert size: 6/03mm


Order data

Order number	260016 6/03
GTIN	4045197651792
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	7 mm
Insert size	3 mm
Centre offset L_3	3.5 mm
Pack of insert screws	269028 19
Head length L_1	10 mm
suitable indexable insert	CC.. 0301..
ISO code toolholder	E06J SCLCR/L03
Overall length L	110 mm
Clamping height L_2	5.8 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	6 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring bar
-----------------	------------

Accessories

Set of insert screws Type 19	269028 19
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500