

Garant
Boring bar HSS, left-hand, Shank \varnothing / insert size: 0610/03mm

Order data

Order number	260023 0610/03
GTIN	4045197652096
Item class	21T

Technical description

Head length L_1	24 mm
Pack of insert screws	269028 13
Neck width L_4	6 mm
suitable indexable insert	CC.. 0301..
Insert size	3 mm
ISO code toolholder	AH0610H SCLCR/L03
Centre offset L_3	2.5 mm
Minimum pre-drill $\varnothing D_{min}$	7 mm
Overall length L	100 mm
Clamping height L_2	9 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 13	269028 13
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500