

**Garant**
**Boring bar HSS, right-hand, Shank  $\varnothing$  / insert size: 0810/06mm**

**Order data**

Order number	260022 0810/06
GTIN	4045197652003
Item class	21T

**Technical description**

Head length $L_1$	32 mm
suitable indexable insert	CC.. 0602..
Centre offset $L_3$	6 mm
Neck width $L_4$	8 mm
Minimum pre-drill $\varnothing D_{\min}$	12 mm
ISO code toolholder	AH0810J SCLCR/L06
Pack of insert screws	269028 7
Insert size	6 mm
Overall length $L$	110 mm
Clamping height $L_2$	9 mm
Setting angle $\kappa$	95 degrees
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500