

Garant
Boring bar HSS, right-hand, Shank \varnothing / insert size: 10/06mm

Order data

Order number	260022 10/06
GTIN	4045197652010
Item class	21T

Technical description

Insert size	6 mm
suitable indexable insert	CC.. 0602..
Minimum pre-drill $\varnothing D_{\min}$	12 mm
Overhang L_1	50 mm
Pack of insert screws	269028 7
Centre offset L_3	6 mm
ISO code toolholder	AH10K SCLCR/L06
Overall length L	125 mm
Clamping height L_2	9 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8

Set of insert screws Type 7

269028 7

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500