

Garant
Boring bar HSS, left-hand, Shank \varnothing / insert size: 08/06mm

Order data

Order number	260023 08/06
GTIN	4045197652119
Item class	21T

Description

Boring bar HSS 08/06 mm Shank $\varnothing D_s$: 8 mm
 ISO code toolholder: AH08K SCLCR/L06
 Setting angle κ : 95 °
 suitable indexable insert: CC.. 0602..
 Minimum pre-drill $\varnothing D_{min}$: 10 mm
 Centre offset L_3 : 5 mm

Technical description

suitable indexable insert	CC.. 0602..
Minimum pre-drill $\varnothing D_{min}$	10 mm
Insert size	6 mm
Centre offset L_3	5 mm
ISO code toolholder	AH08K SCLCR/L06
Overhang L_1	40 mm
Pack of insert screws	269028 7
Overall length L	125 mm
Clamping height L_2	7 mm
Setting angle κ	95 °
Shank $\varnothing D_s$	8 mm
Application type	left-hand

Boring depth up to	5×D
Tool material	HSS
Standard	DIN 8024
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, shank E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Set of insert screws 10 pieces	269413