

Garant
Boring bar HSS, right-hand, Shank \varnothing / insert size: 1012/06mm

Order data

Order number	260022 1012/06
GTIN	4045197652027
Item class	21T

Technical description

Neck width L_4	10 mm
Insert size	6 mm
Centre offset L_3	7 mm
suitable indexable insert	CC.. 0602..
Pack of insert screws	269028 7
Head length L_1	38 mm
Minimum pre-drill $\varnothing D_{\min}$	14 mm
ISO code toolholder	AH1012K SCLCR/L06
Overall length L	125 mm
Clamping height L_2	11 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500