

Garant
Boring bar set carbide, left-hand

Order data

Order number	260019
GTIN	4045197651945
Item class	29W

Description

Boring bar set carbide ISO code toolholder: E08K SCLCR/L06

ISO code toolholder: E10K SCLCR/L06

ISO code toolholder: E12M SCLCR/L06

suitable indexable insert: CC.. 0602..

Minimum pre-drill $\varnothing D_{\min}$: 10 mm

Minimum pre-drill $\varnothing D_{\min}$: 12 mm

Technical description

Pack of insert screws	269028 7
suitable indexable insert	CC.. 0602..
ISO code toolholder	E08K SCLCR/L06
ISO code toolholder	E10K SCLCR/L06
ISO code toolholder	E12M SCLCR/L06
Clamping height L_2	7.6 mm
Clamping height L_2	9.6 mm
Clamping height L_2	11.5 mm
Minimum pre-drill $\varnothing D_{\min}$	10 mm

Minimum pre-drill $\varnothing D_{\min}$	12 mm
Minimum pre-drill $\varnothing D_{\min}$	14 mm
Centre offset L_3	5 mm
Centre offset L_3	6 mm
Centre offset L_3	8 mm
Overall length L	125 mm
Overall length L	125 mm
Overall length L	150 mm
Application type	left-hand
Boring depth up to	8×D
Tool material	Carbide
Standard	DIN 8024
Through-coolant	yes
Type of product	Boring bar

Accessories

Set of insert screws 10 pieces	269413
Set of insert screws Type 7	269028 7