

Garant
Boring bar HSS, left-hand, Shank \varnothing / insert size: 12/06mm

Order data

Order number	260023 12/06
GTIN	4045197652157
Item class	21T

Description

Boring bar HSS 12/06 mm Shank $\varnothing D_s$: 12 mm
 ISO code toolholder: AH12M SCLCR/L06
 Setting angle κ : 95 °
 suitable indexable insert: CC.. 0602..
 Minimum pre-drill $\varnothing D_{\min}$: 14 mm
 Centre offset L_3 : 7 mm

Technical description

Overhang L_1	60 mm
Pack of insert screws	269028 7
Insert size	6 mm
Centre offset L_3	7 mm
suitable indexable insert	CC.. 0602..
ISO code toolholder	AH12M SCLCR/L06
Minimum pre-drill $\varnothing D_{\min}$	14 mm
Overall length L	150 mm
Clamping height L_2	11 mm
Setting angle κ	95 °
Shank $\varnothing D_s$	12 mm
Application type	left-hand

Boring depth up to	5×D
Tool material	HSS
Standard	DIN 8024
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Set of insert screws Type 7	269028 7
PrecisionBit for Torx®, shank E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws 10 pieces	269413