

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 4/03mm

Order data

Order number	260017 4/03
GTIN	4045197651853
Item class	21T

Technical description

suitable indexable insert	CC.. 0301..
Head length L_1	10 mm
Centre offset L_3	2.5 mm
Minimum pre-drill $\varnothing D_{\min}$	5 mm
Pack of insert screws	269028 13
ISO code toolholder	E04G SCLCR/L03
Insert size	3 mm
Overall length L	90 mm
Clamping height L_2	3.8 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	4 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6

Set of insert screws Type 6

269028 6

Set of insert screws Type 13

269028 13

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500