

Garant
Boring bar HSS, left-hand, Shank \varnothing / insert size: 1216/06mm

Order data

Order number	260023 1216/06
GTIN	4045197652164
Item class	21T

Technical description

ISO code toolholder	AH1216M SCLCR/L06
Centre offset L_3	9 mm
suitable indexable insert	CC.. 0602..
Insert size	6 mm
Neck width L_4	12 mm
Head length L_1	50 mm
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	18 mm
Overall length L	150 mm
Clamping height L_2	15 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8
Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500