



## KOMET KUB Trigon® indexable drill Combination shank, 3×D, Ø DC: 32mm



### Order data

Order number	236630 32
GTIN	4047109100527
Item class	24P

### Description

#### Version:

- **Offset-axis drilling: dependent on Ø up to 1.5 mm.**
- **Special manufacturing procedure for extremely large flutes with very high rigidity.**
- **Specific positioning of the indexable inserts for bores free of withdrawal marks and with precise dimensional stability ( $\pm 0.1$  mm as a rule).**
- **Internal coolant supply is directed to the cutting edges (sophisticated geometry, ideal for minimum lubrication).**
- **3 – 10 bar coolant pressure is sufficient.**
- **For stationary and rotating applications.**

#### Application:

With indexable inserts No. 236740 – 237080.

#### Supplied with:

Clamp screws (without indexable inserts).

#### Note:

- **Note! A disc falls off when the drill exits. Risk of injury if the component is rotating! Please take safety precautions.**
- **On request – left-hand cutting; – 2×D, – other Ø; – special types – torsional vibration damper for ABS giving low-vibration machining, with maximum tool life and minimum noise level.**

### Technical description

ISO code indexable insert	WOEX 05T304 24-...
Number of cutting edges Z	1
Reach L <sub>1</sub>	96 mm
Pack of insert screws	239652 8IP2 (1.3 Nm)

achievable maximum $\varnothing$ offset	34 mm
Shank $\varnothing D_s$	32 mm
Shank length $L_s$	60 mm
Series	KUB Trigon®
Nominal $\varnothing D$	32
Maximum adjustment limit $V_{max}$	1 mm
Overhang $L_A$	125 mm
Drill depth for indexable insert drill up to	3xD
Shank	DIN 6535 HE, DIN 6595
Use for drilling	Centre drilling
Use for drilling	limited cross-drilling
Use for drilling	oblique spot drilling
Use for drilling	limited cross-drilling
Use for drilling	Aperture
Use for drilling	oblique exit
Use for drilling	convex
Through-coolant	yes
Type of product	Indexable drill

## Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Torx Plus® insert screw set 10 pieces Drive 8IP2	239652 8IP2
Torque screwdriver, fixed setting set torque 1,3 N·m	211750 1,3