



KOMET KUB Trigon® indexable drill Combination shank, 3×D, Ø DC: 25mm



Order data

| | |
|--------------|---------------|
| Order number | 236630 25 |
| GTIN | 4047109100268 |
| Item class | 24P |

Description

Version:

- **Offset-axis drilling: dependent on Ø up to 1.5 mm.**
- **Special manufacturing procedure for extremely large flutes with very high rigidity.**
- **Specific positioning of the indexable inserts for bores free of withdrawal marks and with precise dimensional stability (± 0.1 mm as a rule).**
- **Internal coolant supply is directed to the cutting edges (sophisticated geometry, ideal for minimum lubrication).**
- **3 – 10 bar coolant pressure is sufficient.**
- **For stationary and rotating applications.**

Application:

With indexable inserts No. 236740 – 237080.

Supplied with:

Clamp screws (without indexable inserts).

Note:

- **Note! A disc falls off when the drill exits. Risk of injury if the component is rotating! Please take safety precautions.**
- **On request – left-hand cutting; – 2×D, – other Ø; – special types – torsional vibration damper for ABS giving low-vibration machining, with maximum tool life and minimum noise level.**

Technical description

| | |
|---------------------------|--------------------|
| Reach L_1 | 75 mm |
| ISO code indexable insert | WOEX 05T304 24-... |
| Number of cutting edges Z | 1 |
| Shank $\varnothing D_s$ | 25 mm |

| | |
|--|------------------------|
| Pack of insert screws | 239652 8IP2 (1.3 Nm) |
| achievable maximum Ø offset | 26 mm |
| Shank length L _s | 56 mm |
| Series | KUB Trigon® |
| Nominal Ø D | 25 |
| Maximum adjustment limit V _{max} | 0.5 mm |
| Overhang L _A | 99 mm |
| Drill depth for indexable insert drill up to | 3×D |
| Shank | DIN 6535 HE, DIN 6595 |
| Use for drilling | Centre drilling |
| Use for drilling | limited cross-drilling |
| Use for drilling | oblique spot drilling |
| Use for drilling | limited cross-drilling |
| Use for drilling | Aperture |
| Use for drilling | oblique exit |
| Use for drilling | convex |
| Through-coolant | yes |
| Type of product | Indexable drill |

Accessories

| | |
|--|-------------|
| PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP | 674252 8IP |
| Torx Plus® insert screw set 10 pieces Drive 8IP2 | 239652 8IP2 |
| Torque screwdriver, fixed setting set torque 1,3 N·m | 211750 1,3 |