



KOMET® UniTurn® grooving boring bar, right-hand, L2 = 30 mm, Ø Dmin/ groove width w: 5/2 mm



Order data

Order number	240166 5/2
GTIN	4047109071865
Item class	24S

Description

Version:

Tool material = BK 82.

From size 5 with internal coolant supply; for smaller diameters, the coolant supply takes place through the toolholder.

Note:

Further sizes and types on request.

Through-coolant: yes

f: 2.25 mm

a: 4.7 mm

Shank Ø d: 8 mm

max. groove depth t_{max} : 1 mm

Suitable toolholder No. 240100: 12/8; 16/8

Technical description

a	4.7 mm
Suitable toolholder No. 240100	12/8; 16/8
for bores from Ø D _{min}	5 mm
Groove width w	2 mm
Shank Ø d	8 mm
f	2.25 mm
max. groove depth t_{max}	1 mm
Through-coolant	yes

Feed f in steel < 500 N/mm ²	0.02 mm/rev.
Usable length	30 mm
Product name attribute	L ₂ = 30 mm
Type of product	Cutter insert for turning

Accessories

KOMET UniTurn® turning toolholder for stationary use (without boring bar) Shank Ø d / Bore Ø d1 12/8 mm	240100 12/8
KOMET UniTurn® turning toolholder for stationary use (without boring bar) Shank Ø d / Bore Ø d1 16/8 mm	240100 16/8