

Garant
Lever lock toolholder, left-hand, Shank / insert size: 16/11mm

Order data

Order number	250611 16/11
GTIN	4045197650535
Item class	21T

Technical description

ISO code toolholder	PDJNR/L 1616H11
Functional width L ₄	20 mm
Lever screw	259018 6
Shim pins pack	259044 4
Shank size	16 mm
suitable indexable insert	DN.. 1104..
Insert size	11 mm
Shim	259031 7
Head length L ₁	25 mm
Lever	259015 7
Shim punches pack	259047 3
Overall length L	100 mm
Series	QuickTurn
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 7	259015 7
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2,5 mm	674242 2,5
Set of shim pins 10 pieces Type 4	259044 4
Shim Type 7	259031 7
Shim punches set 10 pieces Type 3	259047 3
Lever screw Type 6	259018 6
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500