



Cable drum steel core, Type: 25N-4



Order data

Order number	081106 25N-4
GTIN	4007123687633
Item class	08B

Description

Version:

The cable drums meet the specifications set out in DGUV I 203#006 (formerly BGI 608).
Sturdy cable drum with drum body made of sheet metal, double insulated front and back.

Technical description

Cable length	25 m
Number of sockets	4
Drum material	Sheet metal
Length	22 mm
Height	39 mm
Rated current	16 A
Cable class	H07RN-F
Number of sockets type F	4

Data sheet

IP Index of Protection	IP 44
AC supply voltage	230 V
Material cable	Rubber/neoprene
impact-resistant and splash-proof	Category 2 (K2) to BGI
Power supply	Mains-powered
Cable colour	black
Rated power unrolled	3500 (16 A) W
Width	30.5 mm
Cable structure	3G2.5
Number of sockets 230 V	4
Diagnostic system present	yes
Type of product	Cable drum