



Cable drum steel core, Type: 40N-4



Order data

Order number	081106 40N-4
GTIN	4007123687640
Item class	08B

Description

Version:

The cable drums meet the specifications set out in DGUV I 203#006 (formerly BGI 608).
Sturdy cable drum with drum body made of sheet metal, double insulated front and back.

Technical description

Length	22 mm
Material cable	Rubber/neoprene
Drum material	Sheet metal
impact-resistant and splash-proof	Category 2 (K2) to BGI
Cable class	H07RN-F
Cable structure	3G1.5
Height	39 mm
Cable colour	black

Data sheet

IP Index of Protection	IP 44
Number of sockets type F	4
Cable length	40 m
Rated power unrolled	3500 (16 A) W
Width	30.5 mm
Number of sockets	4
Rated current	16 A
Number of sockets 230 V	4
Power supply	Mains-powered
Diagnostic system present	yes
AC supply voltage	230 V
Type of product	Cable drum