



Cable drum steel core, Type: 50B-4



Order data

Order number	081106 50B-4
GTIN	4007123687671
Item class	08B

Description

Version:

The cable drums meet the specifications set out in DGUV I 203#006 (formerly BGI 608).
Sturdy cable drum with drum body made of sheet metal, double insulated front and back.

Technical description

Rated current	16 A
AC supply voltage	230 V
Material cable	PUR (polyurethane)
Cable length	50 m
Number of sockets type F	4
Cable class	H07BQ-F
Cable structure	3G1.5
Length	32 mm

Data sheet

impact-resistant and splash-proof	Category 2 (K2) to BGI
Drum material	Sheet metal
Number of sockets	4
Width	20 mm
Cable colour	red
Number of sockets 230 V	4
Power supply	Mains-powered
Height	40 mm
Diagnostic system present	yes
Rated power unrolled	3500 (16 A) W
IP Index of Protection	IP 44
Type of product	Cable drum