

**Garant**
**Boring bar steel, right-hand, Shank Ø / insert size: 40/12mm**


## Order data

Order number	260032 40/12
GTIN	4045197652294
Item class	21T

## Technical description

Shim	269005 6
suitable indexable insert	CC.. 1204..
Minimum pre-drill Ø $D_{min}$	49 mm
ISO code toolholder	A40T SCLCR/L12
Centre offset $L_3$	27 mm
Pack of insert screws	269028 20
Shim screw	269013 5
Insert size	12 mm
Overall length L	300 mm
Clamping height $L_2$	38.5 mm
Setting angle $\kappa$	95 degrees
Shank Ø $D_s$	40 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

**Accessories**

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim Type 6	269005 6
Shim screw Type 5	269013 5
Set of insert screws Type 20	269028 20
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500